

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204505

Luminaire Tested: **LSR6B40D010BZ EC6B30509035 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204505  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30509035 6LBSB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3312.8 lumens  
Efficiency: N/A  
Efficacy: 79.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204505

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204505

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65																			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204505

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.9	4.2
10°-20°	391.4	11.8
20°-30°	582.2	17.6
30°-40°	677.4	20.4
40°-50°	660.3	19.9
50°-60°	507.9	15.3
60°-70°	280.8	8.5
70°-80°	74.4	2.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1111.5	33.5
0°-40°	1788.9	54.0
0°-60°	2957.1	89.3
0°-90°	3312.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3312.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1461	
5°	1453	138
15°	1386	391
25°	1264	582
35°	1088	677
45°	857	660
55°	567	508
65°	281	281
75°	63	74
85°	0	1
90°	0	



TEST NUMBER: P204505

CATALOG NUMBER: LSR6B40D010BZ EC6B30509035 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1461.4
2.5°	1461.4
5°	1453.0
7.5°	1440.4
10°	1432.0
12.5°	1406.8
15°	1385.8
17.5°	1364.8
20°	1335.4
22.5°	1306.0
25°	1264.0
27.5°	1222.0
30°	1180.0
32.5°	1133.8
35°	1087.6
37.5°	1028.9
40°	978.5
42.5°	923.9
45°	856.7
47.5°	793.7
50°	722.3
52.5°	646.7
55°	566.9
57.5°	491.3
60°	419.9
62.5°	348.6
65°	281.4
67.5°	218.4
70°	159.6
72.5°	109.2
75°	63.0
77.5°	29.4
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)