

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204067

Luminaire Tested: **LE\_6B20D010 EC6B10209035 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204067  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209035 6LBNMW1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1593.1 lumens  
Efficiency: N/A  
Efficacy: 76.6 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204067

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204067

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204067

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBNMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.3	7.6
10°-20°	321.6	20.2
20°-30°	429.3	26.9
30°-40°	346.3	21.7
40°-50°	166.0	10.4
50°-60°	98.4	6.2
60°-70°	65.5	4.1
70°-80°	35.1	2.2
80°-90°	9.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	872.2	54.7
0°-40°	1218.5	76.5
0°-60°	1483.0	93.1
0°-90°	1593.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1593.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1306	
5°	1291	121
15°	1144	322
25°	939	429
35°	554	346
45°	205	166
55°	109	98
65°	66	65
75°	33	35
85°	8	10
90°	0	



TEST NUMBER: P204067

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1306.5
2.5°	1306.5
5°	1291.2
7.5°	1266.0
10°	1230.5
12.5°	1192.5
15°	1144.4
17.5°	1098.9
20°	1048.2
22.5°	995.0
25°	939.4
27.5°	881.1
30°	797.5
32.5°	681.1
35°	554.5
37.5°	438.0
40°	339.2
42.5°	263.4
45°	205.1
47.5°	162.0
50°	136.8
52.5°	121.5
55°	108.9
57.5°	98.8
60°	86.1
62.5°	76.0
65°	65.9
67.5°	55.8
70°	48.1
72.5°	40.5
75°	32.9
77.5°	25.4
80°	20.2
82.5°	15.2
85°	7.6
87.5°	2.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)