

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204687

Luminaire Tested: **LE_6B20D010 EC6B10209035 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209035 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2477.0 lumens
Efficiency: N/A
Efficacy: 119.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204687

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204687

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204687

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	3.8
10°-20°	269.5	10.9
20°-30°	406.0	16.4
30°-40°	483.1	19.5
40°-50°	482.2	19.5
50°-60°	392.1	15.8
60°-70°	241.2	9.7
70°-80°	93.5	3.8
80°-90°	15.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	770.1	31.1
0°-40°	1253.1	50.6
0°-60°	2127.4	85.9
0°-90°	2477.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2477.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	998	
5°	995	95
15°	957	270
25°	884	406
35°	774	483
45°	627	482
55°	439	392
65°	242	241
75°	85	93
85°	12	15
90°	0	



TEST NUMBER: P204687

CATALOG NUMBER: LE_6B20D010 EC6B10209035 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	998.0
2.5°	999.5
5°	995.1
7.5°	989.2
10°	981.9
12.5°	968.6
15°	956.9
17.5°	939.2
20°	920.2
22.5°	902.6
25°	883.5
27.5°	857.1
30°	830.8
32.5°	805.8
35°	773.5
37.5°	738.2
40°	706.0
42.5°	666.4
45°	626.6
47.5°	584.1
50°	538.6
52.5°	491.6
55°	438.9
57.5°	387.5
60°	337.5
62.5°	289.1
65°	242.1
67.5°	198.1
70°	157.0
72.5°	118.9
75°	85.1
77.5°	55.8
80°	33.8
82.5°	20.5
85°	11.8
87.5°	5.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)