

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204479

Luminaire Tested: **LE\_6B20D010 EC6B10209035 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204479  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209035 6LBSB1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2020.4 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204479

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204479

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			76
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			65
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			35
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			32
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			29

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204479

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.1	4.2
10°-20°	238.7	11.8
20°-30°	355.0	17.6
30°-40°	413.2	20.5
40°-50°	402.7	19.9
50°-60°	309.7	15.3
60°-70°	171.2	8.5
70°-80°	45.3	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.8	33.5
0°-40°	1091.0	54.0
0°-60°	1803.5	89.3
0°-90°	2020.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2020.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	891	
5°	886	84
15°	845	239
25°	771	355
35°	663	413
45°	522	403
55°	346	310
65°	172	171
75°	38	45
85°	0	0
90°	0	



TEST NUMBER: P204479

CATALOG NUMBER: LE\_6B20D010 EC6B10209035 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	891.2
2.5°	891.2
5°	886.1
7.5°	878.5
10°	873.4
12.5°	858.0
15°	845.1
17.5°	832.4
20°	814.4
22.5°	796.5
25°	770.9
27.5°	745.2
30°	719.6
32.5°	691.5
35°	663.4
37.5°	627.5
40°	596.8
42.5°	563.5
45°	522.5
47.5°	484.0
50°	440.5
52.5°	394.4
55°	345.8
57.5°	299.6
60°	256.1
62.5°	212.6
65°	171.6
67.5°	133.1
70°	97.4
72.5°	66.6
75°	38.4
77.5°	17.9
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)