

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204191

Luminaire Tested: **LSR6B40D010BZ EC6B30508040 6LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508040 6LBSH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4506.7 lumens
Efficiency: N/A
Efficacy: 107.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204191

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P204191

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204191

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.8	4.9
10°-20°	600.1	13.3
20°-30°	833.3	18.5
30°-40°	909.4	20.2
40°-50°	848.3	18.8
50°-60°	643.9	14.3
60°-70°	352.6	7.8
70°-80°	97.0	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1654.2	36.7
0°-40°	2563.6	56.9
0°-60°	4055.8	90.0
0°-90°	4506.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4506.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2357	
5°	2337	221
15°	2139	600
25°	1811	833
35°	1454	909
45°	1102	848
55°	720	644
65°	352	353
75°	84	97
85°	0	1
90°	0	



TEST NUMBER: P204191

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2357.0
2.5°	2357.0
5°	2337.2
7.5°	2307.4
10°	2262.7
12.5°	2203.2
15°	2138.7
17.5°	2059.3
20°	1984.8
22.5°	1895.5
25°	1811.2
27.5°	1726.8
30°	1632.5
32.5°	1543.2
35°	1453.9
37.5°	1364.6
40°	1280.2
42.5°	1190.9
45°	1101.6
47.5°	1012.3
50°	913.0
52.5°	818.7
55°	719.5
57.5°	625.2
60°	530.9
62.5°	436.7
65°	352.3
67.5°	272.9
70°	203.4
72.5°	138.9
75°	84.4
77.5°	39.7
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)