

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203238

Luminaire Tested: **LE_6B20D010 EC6B10208040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10208040 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1928.8 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203238
CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203238

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92					92			
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85					85			
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78					78			
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72					72			
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66					66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61					61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57					57			
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53					53			
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49					49			
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46					46			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203238

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.5	9.0
10°-20°	451.5	23.4
20°-30°	585.0	30.3
30°-40°	434.3	22.5
40°-50°	183.4	9.5
50°-60°	65.2	3.4
60°-70°	25.1	1.3
70°-80°	8.7	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1211.0	62.8
0°-40°	1645.4	85.3
0°-60°	1893.9	98.2
0°-90°	1928.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1928.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1909	
5°	1867	175
15°	1611	451
25°	1297	585
35°	689	434
45°	226	183
55°	69	65
65°	25	25
75°	8	9
85°	0	1
90°	0	



TEST NUMBER: P203238

CATALOG NUMBER: LE_6B20D010 EC6B10208040 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1908.8
2.5°	1903.2
5°	1867.4
7.5°	1815.1
10°	1751.8
12.5°	1682.9
15°	1611.2
17.5°	1531.4
20°	1459.8
22.5°	1385.4
25°	1297.2
27.5°	1176.1
30°	1032.9
32.5°	864.9
35°	688.6
37.5°	539.9
40°	410.4
42.5°	305.8
45°	225.9
47.5°	165.2
50°	121.2
52.5°	90.9
55°	68.9
57.5°	52.4
60°	41.4
62.5°	30.2
65°	24.8
67.5°	19.2
70°	13.8
72.5°	11.0
75°	8.2
77.5°	5.5
80°	2.8
82.5°	2.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)