

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203058

Luminaire Tested: **LSR6B40D010BZ EC6B30508040 6LBWB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203058  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B40D010BZ EC6B30508040 6LBWB1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57  
W DL3-44.71 W DLE-39.33 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2434.3 lumens  
Efficiency: N/A  
Efficacy: 58.2 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 41.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203058

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBWB1

### Luminous Intensity Polar Plot





TEST NUMBER: P203058

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBWB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92	92	92	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	72	66	61	71	65	61	69	64	61	68	64	60	59	59	59	59
7	78	68	61	56	77	67	61	56	66	60	56	65	60	56	63	59	55	54	54	54	54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50	50	50	50
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46	46	46	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	42	42	42	42

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203058

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBWB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.5	7.1
10°-20°	482.4	19.8
20°-30°	675.7	27.8
30°-40°	645.3	26.5
40°-50°	367.5	15.1
50°-60°	89.8	3.7
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1330.5	54.7
0°-40°	1975.8	81.2
0°-60°	2433.1	100.0
0°-90°	2434.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2434.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1835	
5°	1820	172
15°	1711	482
25°	1478	676
35°	1051	645
45°	471	368
55°	89	90
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203058

CATALOG NUMBER: LSR6B40D010BZ EC6B30508040 6LBWB1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1834.7
2.5°	1834.7
5°	1819.8
7.5°	1799.9
10°	1785.1
12.5°	1755.3
15°	1710.7
17.5°	1671.0
20°	1621.4
22.5°	1557.0
25°	1477.6
27.5°	1388.4
30°	1289.2
32.5°	1170.2
35°	1051.2
37.5°	907.4
40°	753.7
42.5°	609.9
45°	471.1
47.5°	347.1
50°	243.0
52.5°	153.7
55°	89.3
57.5°	39.7
60°	9.9
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)