

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205022

Luminaire Tested: **LSR6B40D010BZ EC6B30509040 6LBSCMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509040 6LBCSMMS1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3728.3 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205022

CATALOG NUMBER: LSR6B40D010BZ EC6B30509040 6LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P205022

CATALOG NUMBER: LSR6B40D010BZ EC6B30509040 6LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205022

CATALOG NUMBER: LSR6B40D010BZ EC6B30509040 6LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.4	4.3
10°-20°	452.7	12.1
20°-30°	661.3	17.7
30°-40°	756.4	20.3
40°-50°	726.9	19.5
50°-60°	561.3	15.1
60°-70°	313.3	8.4
70°-80°	91.2	2.4
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1275.4	34.2
0°-40°	2031.7	54.5
0°-60°	3319.9	89.0
0°-90°	3728.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3728.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1712	
5°	1698	161
15°	1606	453
25°	1437	661
35°	1211	756
45°	948	727
55°	629	561
65°	314	313
75°	80	91
85°	2	4
90°	0	



TEST NUMBER: P205022

CATALOG NUMBER: LSR6B40D010BZ EC6B30509040 6LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1712.1
2.5°	1712.1
5°	1697.7
7.5°	1690.4
10°	1666.3
12.5°	1637.4
15°	1606.0
17.5°	1574.7
20°	1528.9
22.5°	1492.7
25°	1437.2
27.5°	1381.8
30°	1326.3
32.5°	1270.8
35°	1210.6
37.5°	1150.3
40°	1080.3
42.5°	1017.6
45°	947.7
47.5°	868.1
50°	793.4
52.5°	711.4
55°	629.4
57.5°	545.0
60°	465.4
62.5°	385.8
65°	313.5
67.5°	246.0
70°	183.3
72.5°	127.8
75°	79.6
77.5°	41.0
80°	14.5
82.5°	4.8
85°	2.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)