

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205193

Luminaire Tested: **LE\_6B20D010 EC6B10208040 6LBWLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205193  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208040 6LBWL1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2666.4 lumens  
Efficiency: N/A  
Efficacy: 128.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205193

CATALOG NUMBER: LE\_6B20D010 EC6B10208040 6LBWLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205193

CATALOG NUMBER: LE\_6B20D010 EC6B10208040 6LBWLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41				41

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205193

CATALOG NUMBER: LE\_6B20D010 EC6B10208040 6LBWLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.7	6.0
10°-20°	483.0	18.1
20°-30°	728.1	27.3
30°-40°	745.2	27.9
40°-50°	434.2	16.3
50°-60°	99.8	3.7
60°-70°	12.3	0.5
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1371.8	51.4
0°-40°	2117.1	79.4
0°-60°	2651.0	99.4
0°-90°	2666.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2666.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1666	
5°	1675	161
15°	1711	483
25°	1596	728
35°	1209	745
45°	559	434
55°	97	100
65°	9	12
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P205193

CATALOG NUMBER: LE\_6B20D010 EC6B10208040 6LBWLI1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1665.8
2.5°	1662.8
5°	1674.9
7.5°	1686.9
10°	1702.0
12.5°	1705.1
15°	1711.1
17.5°	1705.1
20°	1690.0
22.5°	1641.6
25°	1596.2
27.5°	1523.6
30°	1430.0
32.5°	1333.2
35°	1209.2
37.5°	1070.2
40°	916.0
42.5°	743.8
45°	559.2
47.5°	390.0
50°	257.0
52.5°	163.2
55°	96.8
57.5°	51.4
60°	27.2
62.5°	15.1
65°	9.1
67.5°	9.1
70°	6.0
72.5°	3.0
75°	3.0
77.5°	3.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)