

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205402

Luminaire Tested: **LE_6B20D010 EC6B10209040 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205402
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209040 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2382.8 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205402

CATALOG NUMBER: LE_6B20D010 EC6B10209040 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205402

CATALOG NUMBER: LE_6B20D010 EC6B10209040 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205402

CATALOG NUMBER: LE_6B20D010 EC6B10209040 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.6	5.8
10°-20°	352.7	14.8
20°-30°	449.8	18.9
30°-40°	466.5	19.6
40°-50°	429.8	18.0
50°-60°	323.3	13.6
60°-70°	174.5	7.3
70°-80°	46.9	2.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	941.1	39.5
0°-40°	1407.6	59.1
0°-60°	2160.7	90.7
0°-90°	2382.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2382.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1504	
5°	1481	139
15°	1258	353
25°	977	450
35°	744	466
45°	559	430
55°	362	323
65°	175	175
75°	40	47
85°	0	1
90°	0	



TEST NUMBER: P205402

CATALOG NUMBER: LE_6B20D010 EC6B10209040 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1503.6
2.5°	1498.5
5°	1480.9
7.5°	1447.9
10°	1389.8
12.5°	1331.5
15°	1258.1
17.5°	1189.8
20°	1118.9
22.5°	1045.5
25°	977.1
27.5°	911.2
30°	850.5
32.5°	794.9
35°	744.2
37.5°	696.1
40°	650.5
42.5°	602.5
45°	559.4
47.5°	511.4
50°	463.2
52.5°	412.6
55°	362.0
57.5°	311.4
60°	263.2
62.5°	217.8
65°	174.6
67.5°	134.1
70°	98.8
72.5°	68.4
75°	40.5
77.5°	17.8
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)