

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202518

Luminaire Tested: **LE\_6B20D010 EC6B10208050 6LBSWMH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202518  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10208050 6LBSWMH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2762.1 lumens  
Efficiency: N/A  
Efficacy: 132.8 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202518

CATALOG NUMBER: LE\_6B20D010 EC6B10208050 6LBSWMH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202518

CATALOG NUMBER: LE\_6B20D010 EC6B10208050 6LBSWMH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 94  | 92  | 90  | 88  |    |    |   |
| 2   | 103 | 96  | 90  | 85  | 100 | 94  | 89  | 84  | 91  | 86  | 82  | 87  | 84  | 81  | 84  | 81  | 79  | 77  |    |    |   |
| 3   | 95  | 86  | 79  | 73  | 92  | 84  | 78  | 73  | 81  | 76  | 71  | 79  | 74  | 70  | 76  | 72  | 69  | 67  |    |    |   |
| 4   | 88  | 77  | 70  | 64  | 86  | 76  | 69  | 63  | 74  | 67  | 62  | 71  | 66  | 62  | 69  | 65  | 61  | 59  |    |    |   |
| 5   | 81  | 70  | 62  | 56  | 79  | 69  | 61  | 56  | 67  | 60  | 55  | 65  | 59  | 55  | 63  | 58  | 54  | 52  |    |    |   |
| 6   | 76  | 64  | 56  | 50  | 74  | 63  | 55  | 50  | 61  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 48  | 47  |    |    |   |
| 7   | 70  | 58  | 50  | 45  | 69  | 57  | 50  | 45  | 56  | 49  | 44  | 55  | 48  | 44  | 53  | 48  | 44  | 42  |    |    |   |
| 8   | 66  | 54  | 46  | 40  | 64  | 53  | 45  | 40  | 52  | 45  | 40  | 50  | 44  | 40  | 49  | 44  | 40  | 38  |    |    |   |
| 9   | 62  | 49  | 42  | 37  | 61  | 49  | 42  | 37  | 48  | 41  | 37  | 47  | 41  | 36  | 46  | 40  | 36  | 35  |    |    |   |
| 10  | 58  | 46  | 39  | 34  | 57  | 45  | 38  | 34  | 45  | 38  | 34  | 44  | 38  | 33  | 43  | 37  | 33  | 32  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202518

CATALOG NUMBER: LE\_6B20D010 EC6B10208050 6LBSWMH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 147.8  | 5.4       |
| 10°-20°   | 386.3  | 14.0      |
| 20°-30°   | 512.2  | 18.5      |
| 30°-40°   | 546.3  | 19.8      |
| 40°-50°   | 510.7  | 18.5      |
| 50°-60°   | 389.4  | 14.1      |
| 60°-70°   | 211.8  | 7.7       |
| 70°-80°   | 56.8   | 2.1       |
| 80°-90°   | 0.7    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1046.3 | 37.9      |
| 0°-40°    | 1592.6 | 57.7      |
| 0°-60°    | 2492.8 | 90.2      |
| 0°-90°    | 2762.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2762.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1597 |      |
| 5°  | 1575 | 148  |
| 15° | 1377 | 386  |
| 25° | 1115 | 512  |
| 35° | 873  | 546  |
| 45° | 665  | 511  |
| 55° | 438  | 389  |
| 65° | 212  | 212  |
| 75° | 49   | 57   |
| 85° | 0    | 1    |
| 90° | 0    |      |



TEST NUMBER: P202518

CATALOG NUMBER: LE\_6B20D010 EC6B10208050 6LBSWMH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1597.2 |
| 2.5°  | 1592.1 |
| 5°    | 1575.2 |
| 7.5°  | 1539.8 |
| 10°   | 1499.1 |
| 12.5° | 1441.6 |
| 15°   | 1377.2 |
| 17.5° | 1313.0 |
| 20°   | 1243.6 |
| 22.5° | 1177.6 |
| 25°   | 1115.0 |
| 27.5° | 1049.0 |
| 30°   | 986.4  |
| 32.5° | 925.5  |
| 35°   | 873.0  |
| 37.5° | 820.6  |
| 40°   | 766.5  |
| 42.5° | 717.4  |
| 45°   | 665.0  |
| 47.5° | 607.4  |
| 50°   | 553.2  |
| 52.5° | 495.8  |
| 55°   | 438.2  |
| 57.5° | 375.6  |
| 60°   | 318.1  |
| 62.5° | 264.0  |
| 65°   | 211.5  |
| 67.5° | 164.1  |
| 70°   | 120.1  |
| 72.5° | 82.9   |
| 75°   | 49.1   |
| 77.5° | 22.0   |
| 80°   | 5.1    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)