

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203348

Luminaire Tested: **LE_6B20D010 EC6B10209050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203348
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209050 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1752.4 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203348

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203348

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203348

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	11.4
10°-20°	490.7	28.0
20°-30°	567.7	32.4
30°-40°	362.9	20.7
40°-50°	102.9	5.9
50°-60°	18.3	1.0
60°-70°	7.5	0.4
70°-80°	2.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1258.3	71.8
0°-40°	1621.2	92.5
0°-60°	1742.4	99.4
0°-90°	1752.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1752.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2186	
5°	2147	200
15°	1760	491
25°	1253	568
35°	573	363
45°	119	103
55°	17	18
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203348

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2186.2
2.5°	2183.9
5°	2147.2
7.5°	2081.5
10°	1988.9
12.5°	1881.6
15°	1759.8
17.5°	1633.0
20°	1508.8
22.5°	1386.9
25°	1252.8
27.5°	1106.5
30°	943.2
32.5°	760.5
35°	572.8
37.5°	414.4
40°	287.6
42.5°	190.1
45°	119.4
47.5°	70.6
50°	41.4
52.5°	24.4
55°	17.0
57.5°	14.6
60°	12.1
62.5°	9.8
65°	7.2
67.5°	4.9
70°	4.9
72.5°	2.4
75°	2.4
77.5°	2.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)