

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204378

Luminaire Tested: **LE\_6B20D010 EC6B10209050 6LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B20D010 EC6B10209050 6LBSGPH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2121.4 lumens  
Efficiency: N/A  
Efficacy: 102.0 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204378

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204378

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204378

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.8	4.4
10°-20°	260.4	12.3
20°-30°	379.8	17.9
30°-40°	433.1	20.4
40°-50°	415.5	19.6
50°-60°	318.2	15.0
60°-70°	174.6	8.2
70°-80°	46.5	2.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	732.9	34.6
0°-40°	1166.0	55.0
0°-60°	1899.7	89.5
0°-90°	2121.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2121.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	985	
5°	978	93
15°	924	260
25°	825	380
35°	692	433
45°	540	415
55°	356	318
65°	176	175
75°	41	46
85°	0	1
90°	0	



TEST NUMBER: P204378

CATALOG NUMBER: LE\_6B20D010 EC6B10209050 6LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	985.2
2.5°	982.8
5°	977.6
7.5°	970.0
10°	959.8
12.5°	942.0
15°	924.1
17.5°	903.8
20°	880.9
22.5°	852.9
25°	824.9
27.5°	796.9
30°	761.2
32.5°	728.1
35°	692.5
37.5°	656.9
40°	621.2
42.5°	583.0
45°	539.8
47.5°	496.5
50°	450.6
52.5°	402.2
55°	356.4
57.5°	310.6
60°	262.2
62.5°	216.4
65°	175.6
67.5°	134.9
70°	99.2
72.5°	66.2
75°	40.8
77.5°	17.9
80°	5.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)