

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204812

Luminaire Tested: **LSR6B40D010BZ EC6B30508050 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508050 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4750.3 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204812

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204812

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																																				
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																																				
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																																				
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																																				
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																																				
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																																				
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																																				
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																																				
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																																				
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204812

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.8	3.9
10°-20°	523.3	11.0
20°-30°	787.3	16.6
30°-40°	933.0	19.6
40°-50°	928.5	19.5
50°-60°	748.5	15.8
60°-70°	452.8	9.5
70°-80°	168.1	3.5
80°-90°	25.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1494.4	31.5
0°-40°	2427.4	51.1
0°-60°	4104.3	86.4
0°-90°	4750.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4750.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1940	
5°	1932	184
15°	1854	523
25°	1710	787
35°	1494	933
45°	1209	928
55°	835	748
65°	455	453
75°	153	168
85°	20	25
90°	0	



TEST NUMBER: P204812

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1940.2
2.5°	1940.2
5°	1931.5
7.5°	1925.8
10°	1908.5
12.5°	1879.7
15°	1853.8
17.5°	1825.0
20°	1790.5
22.5°	1755.9
25°	1709.9
27.5°	1661.0
30°	1606.3
32.5°	1554.4
35°	1494.0
37.5°	1430.7
40°	1355.8
42.5°	1283.9
45°	1209.0
47.5°	1125.5
50°	1033.4
52.5°	938.4
55°	834.8
57.5°	742.7
60°	639.0
62.5°	546.9
65°	454.8
67.5°	368.5
70°	287.9
72.5°	215.9
75°	152.6
77.5°	97.9
80°	57.6
82.5°	34.5
85°	20.2
87.5°	8.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)