

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205200

Luminaire Tested: **LE_6B20D010 EC6B10209050 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B20D010 EC6B10209050 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2243.4 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205200

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205200

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92			92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76			76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69			69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63			63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44			44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41			41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205200

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.2	6.0
10°-20°	406.4	18.1
20°-30°	612.6	27.3
30°-40°	627.0	27.9
40°-50°	365.3	16.3
50°-60°	83.9	3.7
60°-70°	10.3	0.5
70°-80°	2.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1154.2	51.4
0°-40°	1781.2	79.4
0°-60°	2230.5	99.4
0°-90°	2243.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2243.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1402	
5°	1409	135
15°	1440	406
25°	1343	613
35°	1017	627
45°	471	365
55°	81	84
65°	8	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P205200

CATALOG NUMBER: LE_6B20D010 EC6B10209050 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1401.5
2.5°	1399.0
5°	1409.1
7.5°	1419.4
10°	1432.0
12.5°	1434.6
15°	1439.6
17.5°	1434.6
20°	1421.9
22.5°	1381.1
25°	1343.0
27.5°	1282.0
30°	1203.1
32.5°	1121.8
35°	1017.4
37.5°	900.4
40°	770.8
42.5°	625.8
45°	470.6
47.5°	328.1
50°	216.2
52.5°	137.4
55°	81.4
57.5°	43.2
60°	22.9
62.5°	12.8
65°	7.6
67.5°	7.6
70°	5.1
72.5°	2.5
75°	2.5
77.5°	2.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)