

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203368

Luminaire Tested: **LSR6B40D010BZ EC6B30508050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508050 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3414.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203368

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203368

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																												
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																												
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																												
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																												
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																												
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																												
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58																												
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55																												
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203368

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.4	11.4
10°-20°	955.9	28.0
20°-30°	1106.0	32.4
30°-40°	707.0	20.7
40°-50°	200.5	5.9
50°-60°	35.8	1.0
60°-70°	14.6	0.4
70°-80°	5.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2451.3	71.8
0°-40°	3158.2	92.5
0°-60°	3394.4	99.4
0°-90°	3414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4259	
5°	4183	389
15°	3428	956
25°	2441	1106
35°	1116	707
45°	233	200
55°	33	36
65°	14	15
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P203368

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	4259.1
2.5°	4254.3
5°	4183.1
7.5°	4054.9
10°	3874.5
12.5°	3665.6
15°	3428.2
17.5°	3181.3
20°	2939.1
22.5°	2701.7
25°	2440.6
27.5°	2155.7
30°	1837.5
32.5°	1481.4
35°	1115.8
37.5°	807.2
40°	560.3
42.5°	370.4
45°	232.7
47.5°	137.7
50°	80.7
52.5°	47.5
55°	33.2
57.5°	28.5
60°	23.7
62.5°	19.0
65°	14.2
67.5°	9.5
70°	9.5
72.5°	4.7
75°	4.7
77.5°	4.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)