

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202647

Luminaire Tested: **LSR6B40D010BZ EC6B30508050 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202647
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508050 6LBMWMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3393.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202647

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202647

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74																			
5	92	83	77	73	90	82	77	73	80	76	72	79	75	71	77	74	71	69																			
6	87	78	72	67	85	77	71	67	76	71	67	74	70	66	73	69	66	64																			
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60																			
8	78	69	63	58	77	68	62	58	67	62	58	66	61	58	65	61	58	56																			
9	75	65	59	55	73	64	59	55	63	58	54	62	58	54	62	57	54	53																			
10	71	61	55	51	70	61	55	51	60	55	51	59	54	51	58	54	51	50																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202647

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.3	10.2
10°-20°	889.0	26.2
20°-30°	1091.9	32.2
30°-40°	748.7	22.1
40°-50°	240.7	7.1
50°-60°	48.8	1.4
60°-70°	19.2	0.6
70°-80°	7.2	0.2
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2327.3	68.6
0°-40°	3076.0	90.7
0°-60°	3365.4	99.2
0°-90°	3393.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3393.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3773	
5°	3701	346
15°	3180	889
25°	2409	1092
35°	1194	749
45°	285	241
55°	49	49
65°	20	19
75°	6	7
85°	0	1
90°	0	



TEST NUMBER: P202647

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3773.3
2.5°	3750.2
5°	3701.3
7.5°	3609.2
10°	3485.4
12.5°	3332.9
15°	3180.4
17.5°	3010.5
20°	2823.5
22.5°	2627.8
25°	2409.0
27.5°	2167.2
30°	1862.2
32.5°	1525.4
35°	1194.4
37.5°	892.2
40°	641.8
42.5°	437.5
45°	284.9
47.5°	175.6
50°	106.5
52.5°	66.2
55°	48.9
57.5°	37.4
60°	28.8
62.5°	23.0
65°	20.1
67.5°	14.4
70°	11.5
72.5°	8.6
75°	5.8
77.5°	5.8
80°	2.9
82.5°	2.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)