

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204709

Luminaire Tested: **LSR6B40D010BZ EC6B30508050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30508050 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4697.3 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204709

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204709

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 110 | 106 | 102 | 99 | 107 | 104 | 100 | 97 | 99 | 97 | 94 | 96 | 93 | 91 | 92 | 90 | 88 | 86 | | | | | | | | | | | | | | | | | | | |
| 2 | 101 | 93 | 87 | 82 | 98 | 92 | 86 | 81 | 88 | 83 | 79 | 85 | 81 | 77 | 82 | 79 | 76 | 74 | | | | | | | | | | | | | | | | | | | |
| 3 | 93 | 83 | 75 | 69 | 90 | 81 | 74 | 69 | 78 | 72 | 67 | 76 | 70 | 66 | 73 | 69 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 4 | 85 | 74 | 66 | 59 | 83 | 72 | 65 | 59 | 70 | 63 | 58 | 68 | 62 | 57 | 66 | 61 | 56 | 54 | | | | | | | | | | | | | | | | | | | |
| 5 | 78 | 66 | 58 | 51 | 76 | 65 | 57 | 51 | 63 | 56 | 51 | 61 | 55 | 50 | 59 | 54 | 49 | 47 | | | | | | | | | | | | | | | | | | | |
| 6 | 73 | 60 | 51 | 45 | 71 | 59 | 51 | 45 | 57 | 50 | 44 | 55 | 49 | 44 | 54 | 48 | 44 | 42 | | | | | | | | | | | | | | | | | | | |
| 7 | 67 | 54 | 46 | 40 | 66 | 54 | 46 | 40 | 52 | 45 | 40 | 51 | 44 | 39 | 49 | 43 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 8 | 63 | 50 | 41 | 36 | 61 | 49 | 41 | 36 | 48 | 41 | 35 | 46 | 40 | 35 | 45 | 39 | 35 | 33 | | | | | | | | | | | | | | | | | | | |
| 9 | 59 | 46 | 38 | 32 | 57 | 45 | 37 | 32 | 44 | 37 | 32 | 43 | 36 | 32 | 42 | 36 | 32 | 30 | | | | | | | | | | | | | | | | | | | |
| 10 | 55 | 42 | 34 | 29 | 54 | 42 | 34 | 29 | 41 | 34 | 29 | 40 | 33 | 29 | 39 | 33 | 29 | 27 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204709

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBPSMW1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 179.3 | 3.8 |
| 10°-20° | 511.2 | 10.9 |
| 20°-30° | 769.8 | 16.4 |
| 30°-40° | 916.0 | 19.5 |
| 40°-50° | 914.3 | 19.5 |
| 50°-60° | 743.6 | 15.8 |
| 60°-70° | 457.4 | 9.7 |
| 70°-80° | 177.2 | 3.8 |
| 80°-90° | 28.4 | 0.6 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1460.3 | 31.1 |
| 0°-40° | 2376.3 | 50.6 |
| 0°-60° | 4034.3 | 85.9 |
| 0°-90° | 4697.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4697.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1893 | |
| 5° | 1887 | 179 |
| 15° | 1815 | 511 |
| 25° | 1676 | 770 |
| 35° | 1467 | 916 |
| 45° | 1188 | 914 |
| 55° | 832 | 744 |
| 65° | 459 | 457 |
| 75° | 161 | 177 |
| 85° | 22 | 28 |
| 90° | 0 | |



TEST NUMBER: P204709

CATALOG NUMBER: LSR6B40D010BZ EC6B30508050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1892.6 |
| 2.5° | 1895.4 |
| 5° | 1887.0 |
| 7.5° | 1875.9 |
| 10° | 1862.0 |
| 12.5° | 1836.9 |
| 15° | 1814.6 |
| 17.5° | 1781.2 |
| 20° | 1745.1 |
| 22.5° | 1711.7 |
| 25° | 1675.5 |
| 27.5° | 1625.4 |
| 30° | 1575.3 |
| 32.5° | 1528.0 |
| 35° | 1466.7 |
| 37.5° | 1399.9 |
| 40° | 1338.7 |
| 42.5° | 1263.6 |
| 45° | 1188.4 |
| 47.5° | 1107.7 |
| 50° | 1021.4 |
| 52.5° | 932.4 |
| 55° | 832.2 |
| 57.5° | 734.8 |
| 60° | 640.1 |
| 62.5° | 548.3 |
| 65° | 459.2 |
| 67.5° | 375.7 |
| 70° | 297.8 |
| 72.5° | 225.4 |
| 75° | 161.4 |
| 77.5° | 105.8 |
| 80° | 64.0 |
| 82.5° | 39.0 |
| 85° | 22.3 |
| 87.5° | 11.1 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)