

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203557

Luminaire Tested: **LE_6B30D010 EC6B30508027 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508027 6LBMMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2833.8 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203557

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203557

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89			89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79			79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71			71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64			64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58			58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53			53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48			48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203557

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.3	6.9
10°-20°	523.2	18.5
20°-30°	702.5	24.8
30°-40°	576.2	20.3
40°-50°	346.1	12.2
50°-60°	230.0	8.1
60°-70°	154.2	5.4
70°-80°	82.9	2.9
80°-90°	23.4	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1421.0	50.1
0°-40°	1997.3	70.5
0°-60°	2573.3	90.8
0°-90°	2833.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2833.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2114	
5°	2079	195
15°	1864	523
25°	1548	703
35°	915	576
45°	438	346
55°	254	230
65°	156	154
75°	78	83
85°	20	23
90°	0	



TEST NUMBER: P203557

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2114.5
2.5°	2098.9
5°	2079.2
7.5°	2036.2
10°	1985.5
12.5°	1922.9
15°	1864.2
17.5°	1794.0
20°	1723.6
22.5°	1645.5
25°	1547.8
27.5°	1430.5
30°	1274.1
32.5°	1098.2
35°	914.6
37.5°	758.2
40°	625.4
42.5°	519.9
45°	437.8
47.5°	371.2
50°	324.4
52.5°	285.4
55°	254.0
57.5°	226.8
60°	203.2
62.5°	175.9
65°	156.4
67.5°	132.9
70°	113.4
72.5°	93.8
75°	78.1
77.5°	62.5
80°	46.9
82.5°	35.1
85°	19.5
87.5°	7.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)