

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203683

Luminaire Tested: **LSR6B40D010BZ EC6B30509050 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B40D010BZ EC6B30509050 6LBNH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-43.02 W DE010-42.54 W D5LT-42.539 W DMX-41.87 W DL2-41.57
W DL3-44.71 W DLE-39.33 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2290.1 lumens
Efficiency: N/A
Efficacy: 54.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 41.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203683

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203683

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93	93																																		
	2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87																																		
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81																																		
	4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75	75																																		
	5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70	70																																		
	6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65																																		
	7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61	61																																		
	8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58																																		
	9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54	54																																		
	10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51	51																																		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203683

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.0	11.5
10°-20°	629.5	27.5
20°-30°	721.2	31.5
30°-40°	484.6	21.2
40°-50°	138.4	6.0
50°-60°	33.9	1.5
60°-70°	12.9	0.6
70°-80°	5.0	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1614.8	70.5
0°-40°	2099.3	91.7
0°-60°	2271.6	99.2
0°-90°	2290.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2290.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2936	
5°	2852	264
15°	2259	630
25°	1574	721
35°	772	485
45°	159	138
55°	38	34
65°	12	13
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P203683

CATALOG NUMBER: LSR6B40D010BZ EC6B30509050 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2935.6
2.5°	2914.7
5°	2852.1
7.5°	2739.3
10°	2601.5
12.5°	2426.2
15°	2259.1
17.5°	2083.7
20°	1908.4
22.5°	1741.3
25°	1574.3
27.5°	1419.8
30°	1240.2
32.5°	1002.2
35°	772.5
37.5°	563.7
40°	388.4
42.5°	254.7
45°	158.7
47.5°	96.0
50°	58.5
52.5°	45.9
55°	37.6
57.5°	29.2
60°	20.9
62.5°	16.7
65°	12.5
67.5°	8.4
70°	8.4
72.5°	4.2
75°	4.2
77.5°	4.2
80°	4.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)