

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204278

Luminaire Tested: **LE\_6B30D010 EC6B30508027 6LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204278  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30508027 6LBSWH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3700.1 lumens  
Efficiency: N/A  
Efficacy: 132.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204278

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204278

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204278

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	203.5	5.5
10°-20°	526.8	14.2
20°-30°	689.0	18.6
30°-40°	729.6	19.7
40°-50°	680.5	18.4
50°-60°	515.4	13.9
60°-70°	279.2	7.5
70°-80°	74.9	2.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1419.4	38.4
0°-40°	2149.0	58.1
0°-60°	3344.9	90.4
0°-90°	3700.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3700.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2207	
5°	2174	204
15°	1883	527
25°	1498	689
35°	1166	730
45°	887	681
55°	579	515
65°	279	279
75°	65	75
85°	0	1
90°	0	



TEST NUMBER: P204278

CATALOG NUMBER: LE\_6B30D010 EC6B30508027 6LBSWH1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2206.8
2.5°	2198.6
5°	2174.4
7.5°	2121.6
10°	2052.9
12.5°	1971.9
15°	1882.8
17.5°	1781.5
20°	1692.5
22.5°	1591.2
25°	1498.1
27.5°	1405.0
30°	1315.9
32.5°	1239.0
35°	1166.1
37.5°	1093.2
40°	1024.4
42.5°	955.6
45°	886.8
47.5°	809.8
50°	732.9
52.5°	656.0
55°	579.0
57.5°	498.0
60°	421.1
62.5°	348.2
65°	279.4
67.5°	214.6
70°	157.9
72.5°	109.4
75°	64.8
77.5°	28.4
80°	8.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)