

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205203

Luminaire Tested: **LE_6B30D010 EC6B30508027 6LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508027 6LBWL1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3570.5 lumens
Efficiency: N/A
Efficacy: 127.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205203

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBWLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205203

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92				92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76				76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69				69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63				63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57				57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52				52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48				48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44				44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205203

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.2	6.0
10°-20°	646.8	18.1
20°-30°	975.0	27.3
30°-40°	997.9	27.9
40°-50°	581.4	16.3
50°-60°	133.6	3.7
60°-70°	16.4	0.5
70°-80°	4.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1837.0	51.4
0°-40°	2834.9	79.4
0°-60°	3549.8	99.4
0°-90°	3570.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3570.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2231	
5°	2243	215
15°	2291	647
25°	2138	975
35°	1619	998
45°	749	581
55°	130	134
65°	12	16
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P205203

CATALOG NUMBER: LE_6B30D010 EC6B30508027 6LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2230.6
2.5°	2226.5
5°	2242.8
7.5°	2258.9
10°	2279.1
12.5°	2283.2
15°	2291.2
17.5°	2283.2
20°	2263.0
22.5°	2198.2
25°	2137.5
27.5°	2040.4
30°	1914.9
32.5°	1785.2
35°	1619.2
37.5°	1433.1
40°	1226.6
42.5°	995.9
45°	748.9
47.5°	522.2
50°	344.1
52.5°	218.6
55°	129.5
57.5°	68.9
60°	36.4
62.5°	20.2
65°	12.1
67.5°	12.1
70°	8.1
72.5°	4.0
75°	4.0
77.5°	4.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)