

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204599

Luminaire Tested: **LE\_6B30D010 EC6B30509727 6LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204599  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30509727 6LBSMW1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2865.1 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204599

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204599

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204599

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	109.4	3.8
10°-20°	311.8	10.9
20°-30°	469.6	16.4
30°-40°	558.7	19.5
40°-50°	557.7	19.5
50°-60°	453.6	15.8
60°-70°	279.0	9.7
70°-80°	108.1	3.8
80°-90°	17.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	890.7	31.1
0°-40°	1449.4	50.6
0°-60°	2460.7	85.9
0°-90°	2865.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2865.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1154	
5°	1151	109
15°	1107	312
25°	1022	470
35°	895	559
45°	725	558
55°	508	454
65°	280	279
75°	98	108
85°	14	17
90°	0	



TEST NUMBER: P204599

CATALOG NUMBER: LE\_6B30D010 EC6B30509727 6LBSMW1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1154.4
2.5°	1156.0
5°	1151.0
7.5°	1144.1
10°	1135.6
12.5°	1120.4
15°	1106.9
17.5°	1086.5
20°	1064.4
22.5°	1044.0
25°	1022.0
27.5°	991.4
30°	960.9
32.5°	932.0
35°	894.6
37.5°	853.9
40°	816.5
42.5°	770.8
45°	724.9
47.5°	675.6
50°	623.0
52.5°	568.8
55°	507.6
57.5°	448.1
60°	390.5
62.5°	334.4
65°	280.1
67.5°	229.1
70°	181.6
72.5°	137.5
75°	98.5
77.5°	64.5
80°	39.0
82.5°	23.8
85°	13.6
87.5°	6.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)