

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204899

Luminaire Tested: **LE_6B30D010 EC6B30508030 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508030 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3428.0 lumens
Efficiency: N/A
Efficacy: 122.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204899

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204899

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88																			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75																			
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65																			
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56																			
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49																			
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43																			
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39																			
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35																			
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31																			
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204899

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.9	4.0
10°-20°	390.0	11.4
20°-30°	586.3	17.1
30°-40°	695.7	20.3
40°-50°	688.5	20.1
50°-60°	540.8	15.8
60°-70°	303.2	8.8
70°-80°	85.2	2.5
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1113.3	32.5
0°-40°	1809.0	52.8
0°-60°	3038.3	88.6
0°-90°	3428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3428.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1448	
5°	1445	137
15°	1384	390
25°	1273	586
35°	1116	696
45°	897	688
55°	610	541
65°	302	303
75°	74	85
85°	0	1
90°	0	



TEST NUMBER: P204899

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1447.5
2.5°	1442.6
5°	1445.0
7.5°	1432.8
10°	1418.0
12.5°	1400.8
15°	1383.6
17.5°	1361.5
20°	1332.0
22.5°	1302.5
25°	1273.0
27.5°	1241.1
30°	1199.2
32.5°	1157.5
35°	1115.8
37.5°	1066.6
40°	1010.0
42.5°	956.0
45°	897.0
47.5°	830.6
50°	761.9
52.5°	683.2
55°	609.5
57.5°	525.9
60°	447.2
62.5°	376.0
65°	302.2
67.5°	238.4
70°	177.0
72.5°	120.4
75°	73.8
77.5°	36.9
80°	9.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)