

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203146

Luminaire Tested: **LE_6B30D010 EC6B30508030 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203146
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508030 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3491.4 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203146

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203146

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203146

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.6	5.3
10°-20°	517.8	14.8
20°-30°	746.1	21.4
30°-40°	774.6	22.2
40°-50°	572.7	16.4
50°-60°	342.1	9.8
60°-70°	207.9	6.0
70°-80°	113.9	3.3
80°-90°	31.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1448.5	41.5
0°-40°	2223.2	63.7
0°-60°	3138.0	89.9
0°-90°	3491.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3491.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1961	
5°	1948	185
15°	1838	518
25°	1626	746
35°	1249	775
45°	737	573
55°	373	342
65°	208	208
75°	106	114
85°	25	32
90°	0	



TEST NUMBER: P203146

CATALOG NUMBER: LE_6B30D010 EC6B30508030 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1960.6
2.5°	1960.6
5°	1947.9
7.5°	1931.0
10°	1905.6
12.5°	1875.9
15°	1837.9
17.5°	1795.5
20°	1753.1
22.5°	1693.9
25°	1626.1
27.5°	1554.1
30°	1461.0
32.5°	1367.8
35°	1249.2
37.5°	1126.4
40°	990.9
42.5°	859.6
45°	736.9
47.5°	626.8
50°	529.4
52.5°	444.6
55°	372.6
57.5°	317.6
60°	271.0
62.5°	237.1
65°	207.5
67.5°	182.1
70°	156.6
72.5°	131.2
75°	105.9
77.5°	84.8
80°	63.5
82.5°	46.6
85°	25.4
87.5°	12.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)