

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274409

Luminaire Tested: **LD6B10DE010W2N2765 EU6B1020W2N902765 6LBS0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274409
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35288)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBS0LI
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, SHALLOW WITH SPECULAR FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.2 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274409

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBSOLI

Luminous Intensity Polar Plot





TEST NUMBER: P274409

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBSOLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	77	69	64	74	68	63		72	67	62		70	65	62	60
5	82	71	63	57	80	70	62	57	67	61	56		66	60	55		64	59	55	53
6	76	64	56	51	74	63	56	51	62	55	50		60	54	50		59	53	49	47
7	71	59	51	46	70	58	51	45	57	50	45		55	49	45		54	49	45	43
8	67	54	47	41	65	54	46	41	52	46	41		51	45	41		50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	40	35	58	46	39	35	45	39	35		45	39	34		44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42204
5°	41724
10°	39609
15°	36561
20°	33422
25°	30263
30°	27564
35°	25502
40°	23838
45°	22208
50°	20228
55°	17710
60°	14784
65°	11593
70°	8107
75°	4386
80°	827
85°	0



TEST NUMBER: P274409

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBSOLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.6	5.8
10°-20°	151.8	14.8
20°-30°	193.5	18.9
30°-40°	200.7	19.6
40°-50°	184.9	18.0
50°-60°	139.1	13.6
60°-70°	75.1	7.3
70°-80°	20.1	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.9	39.5
0°-40°	605.6	59.1
0°-60°	929.6	90.7
0°-90°	1025.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	647	
5°	637	60
15°	541	152
25°	420	194
35°	320	201
45°	241	185
55°	156	139
65°	75	75
75°	17	20
85°	0	0
90°	0	



TEST NUMBER: P274409

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBSOLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	646.9
2.5°	644.7
5°	637.1
7.5°	622.9
10°	597.9
12.5°	572.9
15°	541.3
17.5°	511.9
20°	481.4
22.5°	449.8
25°	420.4
27.5°	392.1
30°	365.9
32.5°	342.0
35°	320.2
37.5°	299.5
40°	279.9
42.5°	259.2
45°	240.7
47.5°	220.0
50°	199.3
52.5°	177.5
55°	155.7
57.5°	134.0
60°	113.3
62.5°	93.7
65°	75.1
67.5°	57.7
70°	42.5
72.5°	29.4
75°	17.4
77.5°	7.6
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)