

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274391

Luminaire Tested: **LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35285)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH SPECULAR FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1035.5 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274391

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P274391

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76		
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69		
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63		
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57		
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52		
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48		
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42204
5°	42595
10°	43789
15°	44882
20°	45565
25°	44624
30°	41833
35°	37401
40°	30293
45°	20040
50°	10129
55°	4277
60°	1383
65°	540
70°	439
75°	302
80°	0
85°	0



TEST NUMBER: P274391

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	6.0
10°-20°	187.6	18.1
20°-30°	282.8	27.3
30°-40°	289.4	27.9
40°-50°	168.6	16.3
50°-60°	38.8	3.7
60°-70°	4.8	0.5
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.7	51.4
0°-40°	822.1	79.4
0°-60°	1029.5	99.4
0°-90°	1035.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	647	
5°	650	62
15°	664	188
25°	620	283
35°	470	289
45°	217	169
55°	38	39
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P274391

CATALOG NUMBER: LD6B10DE010W2N2765 EU6B1020W2N902765 6LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	646.9
2.5°	645.7
5°	650.4
7.5°	655.1
10°	661.0
12.5°	662.1
15°	664.5
17.5°	662.1
20°	656.3
22.5°	637.5
25°	619.9
27.5°	591.7
30°	555.3
32.5°	517.7
35°	469.6
37.5°	415.6
40°	355.7
42.5°	288.8
45°	217.2
47.5°	151.4
50°	99.8
52.5°	63.4
55°	37.6
57.5°	20.0
60°	10.6
62.5°	5.9
65°	3.5
67.5°	3.5
70°	2.3
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)