

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205109

Luminaire Tested: **LE_6B30D010 EC6B30509030 6LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205109
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509030 6LBML1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2822.7 lumens
Efficiency: N/A
Efficacy: 100.8 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205109

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBMLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205109

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																											
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																											
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																											
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																											
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																											
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																											
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																											
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																											
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																											
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																											

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205109

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	325.4	11.5
10°-20°	810.2	28.7
20°-30°	941.8	33.4
30°-40°	576.7	20.4
40°-50°	143.2	5.1
50°-60°	16.8	0.6
60°-70°	6.2	0.2
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2077.4	73.6
0°-40°	2654.1	94.0
0°-60°	2814.1	99.7
0°-90°	2822.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2822.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3532	
5°	3486	325
15°	2908	810
25°	2084	942
35°	903	577
45°	159	143
55°	14	17
65°	7	6
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P205109

CATALOG NUMBER: LE_6B30D010 EC6B30509030 6LBMLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3532.5
2.5°	3528.9
5°	3485.5
7.5°	3391.6
10°	3265.2
12.5°	3099.0
15°	2907.6
17.5°	2701.8
20°	2499.5
22.5°	2297.2
25°	2084.1
27.5°	1838.5
30°	1556.8
32.5°	1228.0
35°	903.0
37.5°	635.8
40°	433.4
42.5°	270.9
45°	158.9
47.5°	90.2
50°	47.0
52.5°	21.6
55°	14.5
57.5°	10.9
60°	10.9
62.5°	7.2
65°	7.2
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)