

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274377

Luminaire Tested: **LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1808-906-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, NARROW DISTRIBUTION WITH HAZE FINISH
Light Source: W2N 2000K-5000K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 837.0 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274377

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P274377

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																												
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88																												
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	83																												
4	99	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77																												
5	94	86	81	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73																												
6	90	81	75	71	88	80	75	71	79	74	71	78	73	70	76	73	70	68																												
7	85	77	71	67	84	76	71	67	75	70	66	74	69	66	73	69	66	64																												
8	82	73	67	63	80	72	67	63	71	66	63	70	66	62	69	65	62	61																												
9	78	69	63	59	77	68	63	59	67	63	59	67	62	59	66	62	59	58																												
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	55																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71261
5°	68088
10°	60893
15°	52611
20°	43888
25°	35645
30°	26985
35°	16055
40°	7929
45°	3132
50°	776
55°	497
60°	285
65°	169
70°	208
75°	0
80°	0
85°	0



TEST NUMBER: P274377

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.4	13.6
10°-20°	257.2	30.7
20°-30°	269.0	32.1
30°-40°	154.0	18.4
40°-50°	36.0	4.3
50°-60°	5.0	0.6
60°-70°	1.8	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	639.7	76.4
0°-40°	793.6	94.8
0°-60°	834.7	99.7
0°-90°	837.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1237	113
15°	927	257
25°	589	269
35°	240	154
45°	40	36
55°	5	5
65°	1	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P274377

CATALOG NUMBER: LD6B15DE010W2N2050 EU6B1020W2N902050 6LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1299.9
2.5°	1282.9
5°	1237.3
7.5°	1169.5
10°	1093.9
12.5°	1013.0
15°	927.0
17.5°	837.0
20°	752.3
22.5°	670.1
25°	589.3
27.5°	513.7
30°	426.3
32.5°	329.9
35°	239.9
37.5°	166.9
40°	110.8
42.5°	70.4
45°	40.4
47.5°	20.9
50°	9.1
52.5°	7.8
55°	5.2
57.5°	3.9
60°	2.6
62.5°	2.6
65°	1.3
67.5°	1.3
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)