

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P274404

Luminaire Tested: **LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P274404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35124)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW
Description: PORTFOLIO 6" W2N RN DOWNLIGHT, WIDE DISTRIBUTION WITH MATTE WHITE FINISH
Light Source: W2N 2700K-6500K CCT TUNING RANGE
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1283.0 lumens
Efficiency: N/A
Efficacy: 58.3 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P274404

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P274404

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77	77	77	77
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68	68	68	68
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60	60	60	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54	54	54	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49	49	49	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	44	44
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40	40	40	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37	37	37	37
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34	34	34	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47006
5°	46878
10°	46393
15°	45618
20°	44732
25°	43018
30°	40446
35°	36565
40°	31009
45°	24985
50°	19741
55°	15571
60°	12996
65°	11779
70°	10987
75°	9806
80°	8754
85°	6962



TEST NUMBER: P274404

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.9	5.3
10°-20°	190.3	14.8
20°-30°	274.2	21.4
30°-40°	284.7	22.2
40°-50°	210.5	16.4
50°-60°	125.7	9.8
60°-70°	76.4	6.0
70°-80°	41.8	3.3
80°-90°	11.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.3	41.5
0°-40°	817.0	63.7
0°-60°	1153.1	89.9
0°-90°	1283.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1283.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	720	
5°	716	68
15°	675	190
25°	598	274
35°	459	285
45°	271	210
55°	137	126
65°	76	76
75°	39	42
85°	9	12
90°	0	



TEST NUMBER: P274404

CATALOG NUMBER: LD6B15DE010W2N2765 EU6B1020W2N902765 6LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	720.5
2.5°	720.5
5°	715.8
7.5°	709.6
10°	700.3
12.5°	689.4
15°	675.4
17.5°	659.8
20°	644.3
22.5°	622.5
25°	597.6
27.5°	571.1
30°	536.9
32.5°	502.6
35°	459.1
37.5°	413.9
40°	364.1
42.5°	315.9
45°	270.8
47.5°	230.3
50°	194.5
52.5°	163.4
55°	136.9
57.5°	116.7
60°	99.6
62.5°	87.1
65°	76.3
67.5°	66.9
70°	57.6
72.5°	48.2
75°	38.9
77.5°	31.1
80°	23.3
82.5°	17.1
85°	9.3
87.5°	4.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)