

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204807

Luminaire Tested: **LE_6B30D010 EC6B30509730 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509730 6LBCSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3028.6 lumens
Efficiency: N/A
Efficacy: 108.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204807

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204807

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																												
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																												
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																												
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																												
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																												
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																												
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																												
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																												
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																												
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204807

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	3.9
10°-20°	333.7	11.0
20°-30°	501.9	16.6
30°-40°	594.8	19.6
40°-50°	592.0	19.5
50°-60°	477.2	15.8
60°-70°	288.7	9.5
70°-80°	107.2	3.5
80°-90°	16.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.8	31.5
0°-40°	1547.6	51.1
0°-60°	2616.7	86.4
0°-90°	3028.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3028.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1237	
5°	1232	117
15°	1182	334
25°	1090	502
35°	952	595
45°	771	592
55°	532	477
65°	290	289
75°	97	107
85°	13	16
90°	0	



TEST NUMBER: P204807

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1237.0
2.5°	1237.0
5°	1231.5
7.5°	1227.8
10°	1216.8
12.5°	1198.5
15°	1181.9
17.5°	1163.6
20°	1141.5
22.5°	1119.5
25°	1090.1
27.5°	1059.0
30°	1024.1
32.5°	991.0
35°	952.5
37.5°	912.1
40°	864.4
42.5°	818.5
45°	770.9
47.5°	717.6
50°	658.9
52.5°	598.2
55°	532.2
57.5°	473.5
60°	407.4
62.5°	348.8
65°	290.0
67.5°	234.9
70°	183.5
72.5°	137.6
75°	97.2
77.5°	62.4
80°	36.8
82.5°	22.0
85°	12.9
87.5°	5.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)