

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204084

Luminaire Tested: **LE_6B30D010 EC6B30509730 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509730 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1990.3 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204084

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204084

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204084

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	7.6
10°-20°	401.8	20.2
20°-30°	536.4	27.0
30°-40°	432.7	21.7
40°-50°	207.4	10.4
50°-60°	122.9	6.2
60°-70°	81.7	4.1
70°-80°	43.7	2.2
80°-90°	12.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1089.7	54.8
0°-40°	1522.4	76.5
0°-60°	1852.8	93.1
0°-90°	1990.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1990.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1632	
5°	1613	152
15°	1430	402
25°	1174	536
35°	693	433
45°	256	207
55°	136	123
65°	82	82
75°	41	44
85°	10	12
90°	0	



TEST NUMBER: P204084

CATALOG NUMBER: LE_6B30D010 EC6B30509730 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1632.2
2.5°	1632.2
5°	1613.2
7.5°	1581.6
10°	1537.4
12.5°	1489.9
15°	1429.8
17.5°	1372.9
20°	1309.6
22.5°	1243.1
25°	1173.6
27.5°	1100.9
30°	996.4
32.5°	850.9
35°	692.8
37.5°	547.2
40°	423.9
42.5°	329.0
45°	256.2
47.5°	202.5
50°	170.9
52.5°	151.9
55°	136.0
57.5°	123.4
60°	107.5
62.5°	94.9
65°	82.2
67.5°	69.6
70°	60.1
72.5°	50.6
75°	41.1
77.5°	31.6
80°	25.2
82.5°	19.0
85°	9.5
87.5°	3.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)