

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203157

Luminaire Tested: **LE\_6B30D010 EC6B30509730 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30509730 6LBWMW1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2606.4 lumens  
Efficiency: N/A  
Efficacy: 93.1 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203157

CATALOG NUMBER: LE\_6B30D010 EC6B30509730 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203157

CATALOG NUMBER: LE\_6B30D010 EC6B30509730 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203157

CATALOG NUMBER: LE\_6B30D010 EC6B30509730 6LBWMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	137.8	5.3
10°-20°	386.6	14.8
20°-30°	557.0	21.4
30°-40°	578.3	22.2
40°-50°	427.5	16.4
50°-60°	255.4	9.8
60°-70°	155.2	6.0
70°-80°	85.0	3.3
80°-90°	23.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1081.4	41.5
0°-40°	1659.6	63.7
0°-60°	2342.5	89.9
0°-90°	2606.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2606.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1464	
5°	1454	138
15°	1372	387
25°	1214	557
35°	932	578
45°	550	428
55°	278	255
65°	155	155
75°	79	85
85°	19	24
90°	0	



TEST NUMBER: P203157

CATALOG NUMBER: LE\_6B30D010 EC6B30509730 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1463.6
2.5°	1463.6
5°	1454.1
7.5°	1441.5
10°	1422.5
12.5°	1400.4
15°	1372.0
17.5°	1340.4
20°	1308.8
22.5°	1264.5
25°	1213.9
27.5°	1160.1
30°	1090.6
32.5°	1021.0
35°	932.5
37.5°	840.9
40°	739.8
42.5°	641.8
45°	550.0
47.5°	467.9
50°	395.1
52.5°	331.9
55°	278.1
57.5°	237.1
60°	202.4
62.5°	177.0
65°	154.9
67.5°	135.9
70°	117.0
72.5°	98.0
75°	79.0
77.5°	63.2
80°	47.4
82.5°	34.8
85°	19.0
87.5°	9.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)