

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202735

Luminaire Tested: **LE_6B30D010 EC6B30508035 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508035 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3348.1 lumens
Efficiency: N/A
Efficacy: 119.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202735

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202735

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202735

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	5.8
10°-20°	553.4	16.5
20°-30°	811.4	24.2
30°-40°	844.5	25.2
40°-50°	584.3	17.5
50°-60°	254.3	7.6
60°-70°	78.0	2.3
70°-80°	23.4	0.7
80°-90°	3.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1559.9	46.6
0°-40°	2404.4	71.8
0°-60°	3243.1	96.9
0°-90°	3348.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3348.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2065	
5°	2056	195
15°	1965	553
25°	1774	811
35°	1366	845
45°	755	584
55°	273	254
65°	74	78
75°	22	23
85°	4	4
90°	0	



TEST NUMBER: P202735

CATALOG NUMBER: LE_6B30D010 EC6B30508035 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2065.0
2.5°	2069.4
5°	2056.4
7.5°	2039.0
10°	2017.2
12.5°	1995.6
15°	1965.2
17.5°	1926.2
20°	1882.8
22.5°	1835.1
25°	1774.4
27.5°	1696.2
30°	1596.5
32.5°	1492.4
35°	1366.5
37.5°	1227.8
40°	1067.2
42.5°	906.8
45°	754.9
47.5°	611.8
50°	485.9
52.5°	368.8
55°	273.2
57.5°	195.2
60°	134.5
62.5°	99.8
65°	73.8
67.5°	56.4
70°	39.0
72.5°	30.4
75°	21.8
77.5°	13.0
80°	8.6
82.5°	4.4
85°	4.4
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)