

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203147

Luminaire Tested: **LE\_6B30D010 EC6B30508035 6LBWMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203147  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30508035 6LBWMW1  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3577.8 lumens  
Efficiency: N/A  
Efficacy: 127.8 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203147

CATALOG NUMBER: LE\_6B30D010 EC6B30508035 6LBWMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203147

CATALOG NUMBER: LE\_6B30D010 EC6B30508035 6LBWMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 111 | 107 | 104 | 100 | 108 | 105 | 102 | 99  | 101 | 98  | 96  | 97  | 95  | 93  | 93  | 92  | 90  | 88  |    |    | 88  |
| 2   | 103 | 96  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 86  | 83  | 88  | 84  | 81  | 85  | 82  | 79  | 77  |    |    | 77  |
| 3   | 95  | 86  | 80  | 74  | 93  | 85  | 79  | 74  | 82  | 77  | 72  | 80  | 75  | 71  | 77  | 73  | 70  | 68  |    |    | 68  |
| 4   | 89  | 78  | 71  | 65  | 86  | 77  | 70  | 65  | 75  | 69  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 60  |    |    | 60  |
| 5   | 82  | 71  | 64  | 58  | 80  | 70  | 63  | 58  | 68  | 62  | 57  | 66  | 61  | 56  | 65  | 60  | 56  | 54  |    |    | 54  |
| 6   | 77  | 65  | 57  | 52  | 75  | 64  | 57  | 52  | 63  | 56  | 51  | 61  | 55  | 51  | 60  | 54  | 50  | 49  |    |    | 49  |
| 7   | 72  | 60  | 52  | 47  | 70  | 59  | 52  | 47  | 58  | 51  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 44  |    |    | 44  |
| 8   | 67  | 55  | 48  | 42  | 66  | 55  | 47  | 42  | 53  | 47  | 42  | 52  | 46  | 42  | 51  | 46  | 42  | 40  |    |    | 40  |
| 9   | 63  | 51  | 44  | 39  | 62  | 51  | 44  | 39  | 50  | 43  | 39  | 49  | 43  | 38  | 48  | 42  | 38  | 37  |    |    | 37  |
| 10  | 60  | 48  | 40  | 36  | 58  | 47  | 40  | 36  | 46  | 40  | 36  | 45  | 40  | 35  | 45  | 39  | 35  | 34  |    |    | 34  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203147

CATALOG NUMBER: LE\_6B30D010 EC6B30508035 6LBWMW1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 189.2  | 5.3       |
| 10°-20°   | 530.6  | 14.8      |
| 20°-30°   | 764.6  | 21.4      |
| 30°-40°   | 793.8  | 22.2      |
| 40°-50°   | 586.9  | 16.4      |
| 50°-60°   | 350.6  | 9.8       |
| 60°-70°   | 213.0  | 6.0       |
| 70°-80°   | 116.7  | 3.3       |
| 80°-90°   | 32.5   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1484.4 | 41.5      |
| 0°-40°    | 2278.2 | 63.7      |
| 0°-60°    | 3215.6 | 89.9      |
| 0°-90°    | 3577.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 3577.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2009 |      |
| 5°  | 1996 | 189  |
| 15° | 1883 | 531  |
| 25° | 1666 | 765  |
| 35° | 1280 | 794  |
| 45° | 755  | 587  |
| 55° | 382  | 351  |
| 65° | 213  | 213  |
| 75° | 108  | 117  |
| 85° | 26   | 32   |
| 90° | 0    |      |



TEST NUMBER: P203147

CATALOG NUMBER: LE\_6B30D010 EC6B30508035 6LBWMW1

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2009.1 |
| 2.5°  | 2009.1 |
| 5°    | 1996.1 |
| 7.5°  | 1978.8 |
| 10°   | 1952.8 |
| 12.5° | 1922.4 |
| 15°   | 1883.4 |
| 17.5° | 1840.0 |
| 20°   | 1796.5 |
| 22.5° | 1735.8 |
| 25°   | 1666.4 |
| 27.5° | 1592.6 |
| 30°   | 1497.1 |
| 32.5° | 1401.6 |
| 35°   | 1280.1 |
| 37.5° | 1154.2 |
| 40°   | 1015.5 |
| 42.5° | 880.9  |
| 45°   | 755.1  |
| 47.5° | 642.2  |
| 50°   | 542.4  |
| 52.5° | 455.6  |
| 55°   | 381.9  |
| 57.5° | 325.5  |
| 60°   | 277.8  |
| 62.5° | 243.0  |
| 65°   | 212.6  |
| 67.5° | 186.6  |
| 70°   | 160.5  |
| 72.5° | 134.5  |
| 75°   | 108.5  |
| 77.5° | 86.8   |
| 80°   | 65.1   |
| 82.5° | 47.8   |
| 85°   | 26.0   |
| 87.5° | 13.0   |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)