

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179742

Luminaire Tested: **LDA6A65835D010TE LARH20SP 6LAL1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P179742  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26678)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A65835D010TE LARH20SP 6LAL1LI  
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5296.2 lumens  
Efficiency: N/A  
Efficacy: 67.9 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.45  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 78  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P179742

CATALOG NUMBER: LDA6A65835D010TE LARH20SP 6LAL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P179742

CATALOG NUMBER: LDA6A65835D010TE LARH20SP 6LAL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	96	94	93	93	93	93
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90	90	90	90
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	89	88	86	86	86	86
5	101	94	90	87	99	94	90	87	92	89	86	91	88	85	89	87	85	83	83	83	83
6	97	91	87	84	96	90	86	83	89	85	83	88	85	82	87	84	82	81	81	81	81
7	95	88	84	80	93	87	83	80	86	83	80	85	82	80	84	81	79	78	78	78	78
8	92	85	81	78	91	84	80	78	83	80	77	83	79	77	82	79	77	76	76	76	76
9	89	82	78	75	88	82	78	75	81	77	75	80	77	75	80	77	74	73	73	73	73
10	87	80	75	73	86	79	75	73	79	75	72	78	75	72	77	74	72	71	71	71	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1281180
5°	1037709
10°	672950
15°	465780
20°	325382
25°	195568
30°	20617
35°	1994
40°	1195
45°	737
50°	716
55°	1023
60°	1173
65°	934
70°	769
75°	763
80°	758
85°	755



TEST NUMBER: P179742

CATALOG NUMBER: LDA6A65835D010TE LARH20SP 6LAL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1593.5	30.1
10°-20°	2308.5	43.6
20°-30°	1325.3	25.0
30°-40°	38.8	0.7
40°-50°	8.3	0.2
50°-60°	9.1	0.2
60°-70°	7.5	0.1
70°-80°	4.1	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5227.3	98.7
0°-40°	5266.2	99.4
0°-60°	5283.6	99.8
0°-90°	5296.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5296.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	23371	
5°	18857	###
15°	8207	2308
25°	3233	1325
35°	30	39
45°	10	8
55°	11	9
65°	7	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P179742

CATALOG NUMBER: LDA6A65835D010TE LARH20SP 6LAL1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	23370.6
2.5°	22094.0
5°	18857.3
7.5°	15570.4
10°	12089.1
12.5°	9866.5
15°	8207.0
17.5°	6941.1
20°	5577.5
22.5°	4372.5
25°	3233.2
27.5°	1530.7
30°	325.7
32.5°	40.6
35°	29.8
37.5°	21.5
40°	16.7
42.5°	13.1
45°	9.5
47.5°	8.4
50°	8.4
52.5°	9.5
55°	10.7
57.5°	10.7
60°	10.7
62.5°	9.5
65°	7.2
67.5°	6.0
70°	4.8
72.5°	4.8
75°	3.6
77.5°	3.6
80°	2.4
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)