

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205004

Luminaire Tested: **LE_6B30D010 EC6B30508040 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508040 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3935.1 lumens
Efficiency: N/A
Efficacy: 140.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205004

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205004

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	83	80	78	76			76
3	94	85	77	72	92	83	76	71	80	74	70	77	73	69	75	71	67	65			65
4	87	76	68	62	84	74	67	61	72	66	61	70	64	60	68	63	59	57			57
5	80	68	60	54	78	67	59	54	65	58	53	63	57	53	61	56	52	50			50
6	74	62	54	48	72	61	53	47	59	52	47	58	51	47	56	51	46	44			44
7	69	56	48	42	67	56	48	42	54	47	42	53	46	42	51	46	41	40			40
8	64	52	44	38	63	51	43	38	50	43	38	48	42	38	47	42	37	36			36
9	60	48	40	35	59	47	40	34	46	39	34	45	39	34	44	38	34	32			32
10	57	44	36	31	55	43	36	31	43	36	31	42	35	31	41	35	31	29			29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205004

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	4.3
10°-20°	477.9	12.1
20°-30°	698.0	17.7
30°-40°	798.3	20.3
40°-50°	767.2	19.5
50°-60°	592.5	15.1
60°-70°	330.7	8.4
70°-80°	96.2	2.4
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1346.2	34.2
0°-40°	2144.5	54.5
0°-60°	3504.1	89.0
0°-90°	3935.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3935.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1807	
5°	1792	170
15°	1695	478
25°	1517	698
35°	1278	798
45°	1000	767
55°	664	592
65°	331	331
75°	84	96
85°	2	4
90°	0	



TEST NUMBER: P205004

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1807.1
2.5°	1807.1
5°	1791.9
7.5°	1784.2
10°	1758.8
12.5°	1728.2
15°	1695.1
17.5°	1662.1
20°	1613.8
22.5°	1575.5
25°	1517.0
27.5°	1458.5
30°	1399.9
32.5°	1341.4
35°	1277.8
37.5°	1214.1
40°	1140.2
42.5°	1074.1
45°	1000.2
47.5°	916.2
50°	837.4
52.5°	750.9
55°	664.4
57.5°	575.2
60°	491.2
62.5°	407.2
65°	330.9
67.5°	259.6
70°	193.5
72.5°	134.9
75°	84.0
77.5°	43.2
80°	15.2
82.5°	5.1
85°	2.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)