

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179695

Luminaire Tested: **LDA6A65840D010TE LARH20SP 6LA1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26676)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65840D010TE LARH20SP 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5971.8 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 78
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179695

CATALOG NUMBER: LDA6A65840D010TE LARH20SP 6LA1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179695

CATALOG NUMBER: LDA6A65840D010TE LARH20SP 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93	93	93	93
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	90	90	90	90
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	87	87	87	87
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84	84	84	84
6	98	91	87	84	96	91	87	84	89	86	83	88	85	83	87	84	82	81	81	81	81
7	95	88	84	81	94	87	83	81	86	83	80	85	82	80	84	82	79	78	78	78	78
8	92	85	81	78	91	85	81	78	84	80	78	83	80	77	82	79	77	76	76	76	76
9	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74	74	74	74
10	87	80	76	73	86	80	76	73	79	75	73	78	75	73	78	75	72	71	71	71	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1321654
5°	1149012
10°	778548
15°	539697
20°	376102
25°	216418
30°	16977
35°	1392
40°	701
45°	473
50°	418
55°	354
60°	406
65°	480
70°	385
75°	254
80°	379
85°	0



TEST NUMBER: P179695

CATALOG NUMBER: LDA6A65840D010TE LARH20SP 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1776.9	29.8
10°-20°	2676.5	44.8
20°-30°	1474.5	24.7
30°-40°	30.5	0.5
40°-50°	4.9	0.1
50°-60°	3.7	0.1
60°-70°	3.2	0.1
70°-80°	1.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5927.9	99.3
0°-40°	5958.4	99.8
0°-60°	5967.0	99.9
0°-90°	5971.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5971.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24109	
5°	20880	###
15°	9509	2676
25°	3578	1474
35°	21	30
45°	6	5
55°	4	4
65°	4	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179695

CATALOG NUMBER: LDA6A65840D010TE LARH20SP 6LA1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	24108.9
2.5°	23387.7
5°	20879.9
7.5°	17747.7
10°	13986.1
12.5°	11517.5
15°	9509.4
17.5°	8016.7
20°	6446.9
22.5°	5042.4
25°	3577.9
27.5°	1526.9
30°	268.2
32.5°	34.3
35°	20.8
37.5°	13.5
40°	9.8
42.5°	7.3
45°	6.1
47.5°	4.9
50°	4.9
52.5°	4.9
55°	3.7
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)