

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204039

Luminaire Tested: **LE_6B10D010 EC6B10209024 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209024 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 692.7 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204039

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204039

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204039

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	7.6
10°-20°	139.8	20.2
20°-30°	186.7	27.0
30°-40°	150.6	21.7
40°-50°	72.2	10.4
50°-60°	42.8	6.2
60°-70°	28.4	4.1
70°-80°	15.3	2.2
80°-90°	4.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.3	54.8
0°-40°	529.9	76.5
0°-60°	644.9	93.1
0°-90°	692.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	692.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	568	
5°	562	53
15°	498	140
25°	408	187
35°	241	151
45°	89	72
55°	47	43
65°	29	28
75°	14	15
85°	3	4
90°	0	



TEST NUMBER: P204039

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	568.1
2.5°	568.1
5°	561.5
7.5°	550.5
10°	535.1
12.5°	518.6
15°	497.6
17.5°	477.9
20°	455.9
22.5°	432.8
25°	408.5
27.5°	383.1
30°	346.9
32.5°	296.1
35°	241.1
37.5°	190.5
40°	147.5
42.5°	114.5
45°	89.1
47.5°	70.5
50°	59.5
52.5°	52.9
55°	47.4
57.5°	43.0
60°	37.4
62.5°	33.0
65°	28.6
67.5°	24.2
70°	20.9
72.5°	17.6
75°	14.4
77.5°	11.0
80°	8.8
82.5°	6.6
85°	3.2
87.5°	1.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)