

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204554

Luminaire Tested: **LE_6B10D010 EC6B10209024 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209024 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1042.4 lumens
Efficiency: N/A
Efficacy: 105.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204554

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204554

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204554

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.8	3.8
10°-20°	113.4	10.9
20°-30°	170.9	16.4
30°-40°	203.3	19.5
40°-50°	202.9	19.5
50°-60°	165.0	15.8
60°-70°	101.5	9.7
70°-80°	39.3	3.8
80°-90°	6.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.1	31.1
0°-40°	527.3	50.6
0°-60°	895.2	85.9
0°-90°	1042.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1042.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	420	
5°	419	40
15°	403	113
25°	372	171
35°	326	203
45°	264	203
55°	185	165
65°	102	101
75°	36	39
85°	5	6
90°	0	



TEST NUMBER: P204554

CATALOG NUMBER: LE_6B10D010 EC6B10209024 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	420.0
2.5°	420.6
5°	418.8
7.5°	416.2
10°	413.2
12.5°	407.6
15°	402.8
17.5°	395.2
20°	387.2
22.5°	379.9
25°	371.8
27.5°	360.8
30°	349.6
32.5°	339.1
35°	325.5
37.5°	310.6
40°	297.1
42.5°	280.4
45°	263.8
47.5°	245.9
50°	226.6
52.5°	206.9
55°	184.6
57.5°	163.0
60°	142.0
62.5°	121.6
65°	101.9
67.5°	83.4
70°	66.1
72.5°	50.0
75°	35.9
77.5°	23.5
80°	14.2
82.5°	8.6
85°	5.0
87.5°	2.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)