

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202530

Luminaire Tested: **LE_6B30D010 EC6B30508040 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202530
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508040 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4021.1 lumens
Efficiency: N/A
Efficacy: 143.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202530

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202530

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	88			
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	84	81	79	77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42			
8	66	54	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38			
9	62	49	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35			
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202530

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	5.3
10°-20°	562.4	14.0
20°-30°	745.7	18.5
30°-40°	795.4	19.8
40°-50°	743.5	18.5
50°-60°	567.0	14.1
60°-70°	308.4	7.7
70°-80°	82.7	2.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1523.2	37.9
0°-40°	2318.5	57.7
0°-60°	3629.0	90.2
0°-90°	4021.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4021.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2325	
5°	2293	215
15°	2005	562
25°	1623	746
35°	1271	795
45°	968	743
55°	638	567
65°	308	308
75°	71	83
85°	0	1
90°	0	



TEST NUMBER: P202530

CATALOG NUMBER: LE_6B30D010 EC6B30508040 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2325.2
2.5°	2317.8
5°	2293.1
7.5°	2241.5
10°	2182.4
12.5°	2098.6
15°	2005.0
17.5°	1911.4
20°	1810.4
22.5°	1714.4
25°	1623.2
27.5°	1527.1
30°	1436.0
32.5°	1347.4
35°	1271.0
37.5°	1194.6
40°	1115.8
42.5°	1044.4
45°	968.0
47.5°	884.2
50°	805.5
52.5°	721.8
55°	638.0
57.5°	546.9
60°	463.1
62.5°	384.2
65°	307.9
67.5°	238.9
70°	174.9
72.5°	120.8
75°	71.4
77.5°	32.0
80°	7.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)