

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204653

Luminaire Tested: **LE_6B10D010 EC6B10208027 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10208027 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1380.4 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204653
CATALOG NUMBER: LE_6B10D010 EC6B10208027 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204653

CATALOG NUMBER: LE_6B10D010 EC6B10208027 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204653

CATALOG NUMBER: LE_6B10D010 EC6B10208027 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	3.8
10°-20°	150.2	10.9
20°-30°	226.2	16.4
30°-40°	269.2	19.5
40°-50°	268.7	19.5
50°-60°	218.5	15.8
60°-70°	134.4	9.7
70°-80°	52.1	3.8
80°-90°	8.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	429.2	31.1
0°-40°	698.3	50.6
0°-60°	1185.6	85.9
0°-90°	1380.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1380.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	556	
5°	555	53
15°	533	150
25°	492	226
35°	431	269
45°	349	269
55°	245	219
65°	135	134
75°	48	52
85°	6	8
90°	0	



TEST NUMBER: P204653

CATALOG NUMBER: LE_6B10D010 EC6B10208027 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	556.2
2.5°	557.0
5°	554.6
7.5°	551.2
10°	547.2
12.5°	539.9
15°	533.2
17.5°	523.5
20°	512.9
22.5°	503.0
25°	492.4
27.5°	477.6
30°	463.0
32.5°	449.0
35°	431.0
37.5°	411.4
40°	393.4
42.5°	371.4
45°	349.2
47.5°	325.5
50°	300.1
52.5°	274.0
55°	244.6
57.5°	216.0
60°	188.1
62.5°	161.1
65°	135.0
67.5°	110.4
70°	87.5
72.5°	66.2
75°	47.5
77.5°	31.1
80°	18.9
82.5°	11.5
85°	6.5
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)