

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204343

Luminaire Tested: **LE\_6B10D010 EC6B10208027 6LBSGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204343  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B10D010 EC6B10208027 6LBSGPH1  
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT  
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W  
DL3-11.1 W DLE-11.39 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1214.5 lumens  
Efficiency: N/A  
Efficacy: 122.7 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204343

CATALOG NUMBER: LE\_6B10D010 EC6B10208027 6LBSGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204343

CATALOG NUMBER: LE\_6B10D010 EC6B10208027 6LBSGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204343

CATALOG NUMBER: LE\_6B10D010 EC6B10208027 6LBSGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.1	4.4
10°-20°	149.1	12.3
20°-30°	217.4	17.9
30°-40°	248.0	20.4
40°-50°	237.8	19.6
50°-60°	182.1	15.0
60°-70°	100.0	8.2
70°-80°	26.6	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	419.6	34.5
0°-40°	667.6	55.0
0°-60°	1087.5	89.5
0°-90°	1214.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1214.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	564	
5°	560	53
15°	529	149
25°	472	217
35°	396	248
45°	309	238
55°	204	182
65°	101	100
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P204343

CATALOG NUMBER: LE\_6B10D010 EC6B10208027 6LBSGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	564.1
2.5°	562.6
5°	559.8
7.5°	555.4
10°	549.5
12.5°	539.2
15°	529.1
17.5°	517.4
20°	504.4
22.5°	488.2
25°	472.2
27.5°	456.2
30°	435.8
32.5°	416.9
35°	396.5
37.5°	376.0
40°	355.6
42.5°	333.8
45°	309.0
47.5°	284.2
50°	258.0
52.5°	230.2
55°	204.0
57.5°	177.9
60°	150.1
62.5°	123.9
65°	100.6
67.5°	77.2
70°	56.9
72.5°	37.9
75°	23.4
77.5°	10.2
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)