

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203360

Luminaire Tested: **LE\_6B30D010 EC6B30509040 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203360  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B30D010 EC6B30509040 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W  
DL3-29.67 W DLE-29.73 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2530.1 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 28  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203360

CATALOG NUMBER: LE\_6B30D010 EC6B30509040 6LBMWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P203360

CATALOG NUMBER: LE\_6B30D010 EC6B30509040 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203360

CATALOG NUMBER: LE\_6B30D010 EC6B30509040 6LBMWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	288.5	11.4
10°-20°	708.4	28.0
20°-30°	819.6	32.4
30°-40°	523.9	20.7
40°-50°	148.5	5.9
50°-60°	26.5	1.0
60°-70°	10.8	0.4
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1816.6	71.8
0°-40°	2340.5	92.5
0°-60°	2515.6	99.4
0°-90°	2530.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2530.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3156	
5°	3100	289
15°	2541	708
25°	1809	820
35°	827	524
45°	172	149
55°	25	27
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P203360

CATALOG NUMBER: LE\_6B30D010 EC6B30509040 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3156.4
2.5°	3152.9
5°	3100.0
7.5°	3005.0
10°	2871.4
12.5°	2716.5
15°	2540.6
17.5°	2357.6
20°	2178.1
22.5°	2002.2
25°	1808.6
27.5°	1597.5
30°	1361.8
32.5°	1097.9
35°	826.9
37.5°	598.2
40°	415.2
42.5°	274.5
45°	172.4
47.5°	102.0
50°	59.9
52.5°	35.2
55°	24.6
57.5°	21.1
60°	17.6
62.5°	14.1
65°	10.5
67.5°	7.0
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)