

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P202948

Luminaire Tested: **LE_6B30D010 EC6B30509040 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509040 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2133.6 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202948

CATALOG NUMBER: LE_6B30D010 EC6B30509040 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202948

CATALOG NUMBER: LE_6B30D010 EC6B30509040 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82				82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74				74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56				56
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51				51
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47				47
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43				43
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40				40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202948

CATALOG NUMBER: LE_6B30D010 EC6B30509040 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.6	6.4
10°-20°	383.1	18.0
20°-30°	548.1	25.7
30°-40°	546.3	25.6
40°-50°	348.0	16.3
50°-60°	128.3	6.0
60°-70°	32.1	1.5
70°-80°	9.7	0.5
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1067.8	50.0
0°-40°	1614.0	75.6
0°-60°	2090.3	98.0
0°-90°	2133.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2133.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1450	
5°	1443	137
15°	1362	383
25°	1197	548
35°	888	546
45°	448	348
55°	136	128
65°	29	32
75°	7	10
85°	0	1
90°	0	



TEST NUMBER: P202948

CATALOG NUMBER: LE_6B30D010 EC6B30509040 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1450.0
2.5°	1450.0
5°	1442.8
7.5°	1428.0
10°	1409.6
12.5°	1387.6
15°	1362.0
17.5°	1328.9
20°	1292.2
22.5°	1251.9
25°	1196.8
27.5°	1138.0
30°	1060.9
32.5°	980.1
35°	888.4
37.5°	778.2
40°	664.5
42.5°	554.4
45°	447.9
47.5°	352.4
50°	264.4
52.5°	194.6
55°	135.9
57.5°	88.1
60°	58.8
62.5°	40.4
65°	29.4
67.5°	22.0
70°	18.4
72.5°	11.0
75°	7.4
77.5°	7.4
80°	3.6
82.5°	3.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)