

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203252

Luminaire Tested: **LE_6B30D010 EC6B30508050 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30508050 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2795.3 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203252
CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBMH1

Luminous Intensity Polar Plot






TEST NUMBER: P203252

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203252

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.9	9.0
10°-20°	654.3	23.4
20°-30°	847.8	30.3
30°-40°	629.4	22.5
40°-50°	265.7	9.5
50°-60°	94.4	3.4
60°-70°	36.4	1.3
70°-80°	12.6	0.5
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1755.0	62.8
0°-40°	2384.5	85.3
0°-60°	2744.6	98.2
0°-90°	2795.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2795.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2766	
5°	2706	253
15°	2335	654
25°	1880	848
35°	998	629
45°	327	266
55°	100	94
65°	36	36
75°	12	13
85°	0	2
90°	0	



TEST NUMBER: P203252

CATALOG NUMBER: LE_6B30D010 EC6B30508050 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2766.1
2.5°	2758.2
5°	2706.2
7.5°	2630.5
10°	2538.6
12.5°	2438.9
15°	2335.1
17.5°	2219.4
20°	2115.5
22.5°	2007.8
25°	1880.0
27.5°	1704.4
30°	1496.9
32.5°	1253.4
35°	997.9
37.5°	782.4
40°	594.8
42.5°	443.1
45°	327.2
47.5°	239.5
50°	175.6
52.5°	131.8
55°	99.8
57.5°	75.9
60°	59.9
62.5°	43.9
65°	35.9
67.5°	28.0
70°	20.0
72.5°	16.0
75°	12.0
77.5°	8.0
80°	4.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)