

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P35126

Luminaire Tested: **LE_6B10D010 EC6B10209027 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35126
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209027 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 898.7 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35126

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P35126

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73148
5°	72117
10°	67572
15°	60957
20°	53723
25°	46250
30°	36446
35°	23399
40°	12562
45°	5647
50°	2152
55°	1001
60°	809
65°	587
70°	477
75°	302
80°	0
85°	0



TEST NUMBER: P35126

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.5	11.4
10°-20°	251.7	28.0
20°-30°	291.2	32.4
30°-40°	186.1	20.7
40°-50°	52.7	5.9
50°-60°	9.4	1.0
60°-70°	3.9	0.4
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.3	71.8
0°-40°	831.4	92.5
0°-60°	893.6	99.4
0°-90°	898.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1121	
5°	1101	103
15°	902	252
25°	642	291
35°	294	186
45°	61	53
55°	9	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P35126

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1121.2
2.5°	1120.0
5°	1101.2
7.5°	1067.5
10°	1020.0
12.5°	965.0
15°	902.5
17.5°	837.5
20°	773.8
22.5°	711.2
25°	642.5
27.5°	567.5
30°	483.8
32.5°	390.0
35°	293.8
37.5°	212.5
40°	147.5
42.5°	97.5
45°	61.2
47.5°	36.2
50°	21.2
52.5°	12.5
55°	8.8
57.5°	7.5
60°	6.2
62.5°	5.0
65°	3.8
67.5°	2.5
70°	2.5
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)