

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P35131

Luminaire Tested: **LE_6B10D010 EC6B10209027 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P35131
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B10D010 EC6B10209027 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 734.7 lumens
Efficiency: N/A
Efficacy: 75.7 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P35131

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P35131

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70			
7	87	78	73	69	85	77	72	69	76	72	68	75	71	68	74	70	67	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94110
5°	89066
10°	74276
15°	57073
20°	42698
25°	33293
30°	25900
35°	16327
40°	8091
45°	2999
50°	629
55°	432
60°	326
65°	185
70°	229
75°	0
80°	0
85°	0



TEST NUMBER: P35131

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.1	16.6
10°-20°	234.6	31.9
20°-30°	213.3	29.0
30°-40°	129.3	17.6
40°-50°	29.4	4.0
50°-60°	3.8	0.5
60°-70°	1.7	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	570.1	77.6
0°-40°	699.4	95.2
0°-60°	732.6	99.7
0°-90°	734.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1442	
5°	1360	122
15°	845	235
25°	462	213
35°	205	129
45°	32	29
55°	4	4
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P35131

CATALOG NUMBER: LE_6B10D010 EC6B10209027 6LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1442.5
2.5°	1425.0
5°	1360.0
7.5°	1255.0
10°	1121.2
12.5°	982.5
15°	845.0
17.5°	720.0
20°	615.0
22.5°	530.0
25°	462.5
27.5°	402.5
30°	343.8
32.5°	275.0
35°	205.0
37.5°	143.8
40°	95.0
42.5°	58.8
45°	32.5
47.5°	15.0
50°	6.2
52.5°	5.0
55°	3.8
57.5°	3.8
60°	2.5
62.5°	2.5
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)