

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205011

Luminaire Tested: **LE_6B30D010 EC6B30509050 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509050 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3310.9 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205011

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P205011

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 111 | 107 | 103 | 100 | 108 | 105 | 101 | 98 | 100 | 98 | 95 | 97 | 94 | 92 | 93 | 91 | 90 | 88 | 88 | 88 | 88 |
| 2 | 102 | 95 | 89 | 84 | 100 | 93 | 88 | 83 | 90 | 85 | 81 | 86 | 83 | 79 | 83 | 80 | 78 | 76 | 76 | 76 | 76 |
| 3 | 94 | 85 | 77 | 72 | 92 | 83 | 76 | 71 | 80 | 74 | 70 | 77 | 73 | 69 | 75 | 71 | 67 | 65 | 65 | 65 | 65 |
| 4 | 87 | 76 | 68 | 62 | 84 | 74 | 67 | 61 | 72 | 66 | 61 | 70 | 64 | 60 | 68 | 63 | 59 | 57 | 57 | 57 | 57 |
| 5 | 80 | 68 | 60 | 54 | 78 | 67 | 59 | 54 | 65 | 58 | 53 | 63 | 57 | 53 | 61 | 56 | 52 | 50 | 50 | 50 | 50 |
| 6 | 74 | 62 | 54 | 48 | 72 | 61 | 53 | 47 | 59 | 52 | 47 | 58 | 51 | 47 | 56 | 51 | 46 | 44 | 44 | 44 | 44 |
| 7 | 69 | 56 | 48 | 42 | 67 | 56 | 48 | 42 | 54 | 47 | 42 | 53 | 46 | 42 | 51 | 46 | 41 | 40 | 40 | 40 | 40 |
| 8 | 64 | 52 | 44 | 38 | 63 | 51 | 43 | 38 | 50 | 43 | 38 | 48 | 42 | 38 | 47 | 42 | 37 | 36 | 36 | 36 | 36 |
| 9 | 60 | 48 | 40 | 35 | 59 | 47 | 40 | 34 | 46 | 39 | 34 | 45 | 39 | 34 | 44 | 38 | 34 | 32 | 32 | 32 | 32 |
| 10 | 57 | 44 | 36 | 31 | 55 | 43 | 36 | 31 | 43 | 36 | 31 | 42 | 35 | 31 | 41 | 35 | 31 | 29 | 29 | 29 | 29 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205011

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBCS1MMS

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 143.3 | 4.3 |
| 10°-20° | 402.1 | 12.1 |
| 20°-30° | 587.3 | 17.7 |
| 30°-40° | 671.7 | 20.3 |
| 40°-50° | 645.5 | 19.5 |
| 50°-60° | 498.5 | 15.1 |
| 60°-70° | 278.2 | 8.4 |
| 70°-80° | 81.0 | 2.4 |
| 80°-90° | 3.5 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1132.6 | 34.2 |
| 0°-40° | 1804.3 | 54.5 |
| 0°-60° | 2948.2 | 89.0 |
| 0°-90° | 3310.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 3310.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1520 | |
| 5° | 1508 | 143 |
| 15° | 1426 | 402 |
| 25° | 1276 | 587 |
| 35° | 1075 | 672 |
| 45° | 842 | 646 |
| 55° | 559 | 498 |
| 65° | 278 | 278 |
| 75° | 71 | 81 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P205011

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1520.5 |
| 2.5° | 1520.5 |
| 5° | 1507.6 |
| 7.5° | 1501.1 |
| 10° | 1479.8 |
| 12.5° | 1454.0 |
| 15° | 1426.2 |
| 17.5° | 1398.4 |
| 20° | 1357.8 |
| 22.5° | 1325.6 |
| 25° | 1276.4 |
| 27.5° | 1227.1 |
| 30° | 1177.8 |
| 32.5° | 1128.5 |
| 35° | 1075.0 |
| 37.5° | 1021.5 |
| 40° | 959.4 |
| 42.5° | 903.8 |
| 45° | 841.6 |
| 47.5° | 770.9 |
| 50° | 704.5 |
| 52.5° | 631.8 |
| 55° | 558.9 |
| 57.5° | 484.0 |
| 60° | 413.2 |
| 62.5° | 342.6 |
| 65° | 278.4 |
| 67.5° | 218.4 |
| 70° | 162.8 |
| 72.5° | 113.5 |
| 75° | 70.6 |
| 77.5° | 36.4 |
| 80° | 12.9 |
| 82.5° | 4.2 |
| 85° | 2.1 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)