

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204391

Luminaire Tested: **LE_6B30D010 EC6B30509050 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204391
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B30D010 EC6B30509050 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3076.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204391

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204391

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	91	90	88			88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76			76
3	94	85	78	72	92	83	77	71	80	75	70	78	73	69	75	71	68	66			66
4	87	76	68	62	85	75	67	62	72	66	61	70	65	60	68	63	59	57			57
5	80	68	60	54	78	67	60	54	65	59	53	63	58	53	62	56	52	50			50
6	74	62	54	48	73	61	53	48	59	52	47	58	52	47	56	51	47	45			45
7	69	57	48	43	68	56	48	43	54	47	42	53	47	42	52	46	42	40			40
8	65	52	44	38	63	51	44	38	50	43	38	49	42	38	48	42	38	36			36
9	60	48	40	35	59	47	40	35	46	39	35	45	39	34	44	38	34	32			32
10	57	44	37	32	56	44	36	32	43	36	31	42	36	31	41	35	31	30			30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204391

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.5	4.4
10°-20°	377.6	12.3
20°-30°	550.7	17.9
30°-40°	628.0	20.4
40°-50°	602.4	19.6
50°-60°	461.3	15.0
60°-70°	253.2	8.2
70°-80°	67.4	2.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1062.7	34.5
0°-40°	1690.7	55.0
0°-60°	2754.5	89.5
0°-90°	3076.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3076.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1429	
5°	1418	135
15°	1340	378
25°	1196	551
35°	1004	628
45°	783	602
55°	517	461
65°	255	253
75°	59	67
85°	0	1
90°	0	



TEST NUMBER: P204391

CATALOG NUMBER: LE_6B30D010 EC6B30509050 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1428.6
2.5°	1424.9
5°	1417.5
7.5°	1406.5
10°	1391.8
12.5°	1365.9
15°	1340.0
17.5°	1310.5
20°	1277.2
22.5°	1236.6
25°	1196.0
27.5°	1155.5
30°	1103.8
32.5°	1055.8
35°	1004.1
37.5°	952.4
40°	900.8
42.5°	845.4
45°	782.6
47.5°	719.9
50°	653.4
52.5°	583.2
55°	516.8
57.5°	450.4
60°	380.2
62.5°	313.8
65°	254.8
67.5°	195.6
70°	144.0
72.5°	96.0
75°	59.1
77.5°	25.9
80°	7.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)